



Contents

- Conduit
- Coiled Cord Assembly
- Power Wire Harness
- Pigtail Adapter
- Normally Open Low Profile Switch
- Hardware for Fastening to Mast and Carriage

Catalog Order No.	Overall Lowered Height ^③ OAL	Mast ^① Maximum Fork Height MFH	Conductors	Mounting Clearance Dimensions				Wire Size
				A	B	C	D	
6029814	≤77"	166"	2	51"	6"	4.5"	2.5"	20 AWG ^②
6001133	78"-83"	189"	2	57"	6"	4.5"	2.5"	20 AWG ^②
6029348	84"-93"	218"	2	64"	6"	4.5"	2.5"	20 AWG ^②
228174	94"-101"	240"	2	70"	6"	4.5"	2.5"	20 AWG ^②
6016846	102"-120"	320"	2	83"	6"	4.5"	2.5"	20 AWG ^②

- ① Dual and triple lift mast only. Not available for quad masts.
- ② 5 amps max at 12 volts
- ③ OAL and MFH dimensions are guidelines. Refer to mounting clearance requirements to verify that power supply will fit on mast.
- ④ Termination point must be attached to a non-sideshifting member of the mast carriage. If using an integral carriage, special bracketing may be required.
- ▶ Hose reel adaption mounting **kit 6008338**
- ▶ For best performance, the Power Supply must be mounted in the zone above represented by the dashed lines and as close to the top of the channels as possible. Please verify that this free area is available on your lift truck.
- ▶ Bracket available to stack two power cords beside each other